

# COMPACTA

1298UOI014P80

EAN  
Order number

4031582300024  
00021119



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Product type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	33.07 lb
Load capacity Static	66.14 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	0.53 in
Overall width	0.75 in
Overall weight	0.02 lb

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	0.55 in
Tread width	0.5512 in
Body width	0.55 in
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Steel sheet, light
Fork shape	Straight
Color	Blue passivated
Dome diameter	0.75 in

## FITTING

Fitting type	Round plate
Plate hole length (Maximum)	0.79 in
Plate hole width (Maximum)	0.79 in
Plate hole diameter	0.1 in

# COMPACTA

1298UOI014P80

EAN  
Order number

4031582300024  
00021119



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

