



BETTER MOBILITY. BETTER LIFE.

1310POO036P30-10 (6)

EAN 4031582222814

Swivel castor, bolt hole. Wheel centre made of Polypropylene, plain bearing



Picture may differ from original product

Technical Data

Wheel diameter	36 mm
Wheel width	16 mm
Centre hole	10 mm
Offset	13 mm
Overall height	50 mm
Temperature	-20 / + 60 °C
Weight	0.065 kg
Hardness of tread	Shore D 65
Load capacity	20 kg
Load capacity (static)	40 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ○ ○ ○