

AGILA

1438PVH050P60-67x48

EAN 3700001796748

Fixed caster, plate fitting.

Wheel center made of Polypropylene, Tread: solid rubber, black, plain bearing, threadguard



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	50 mm
Wheel width	21 mm
Plate size	67 x 48 mm
Plate hole centers	55 x 30 mm
Plate hole	6 mm
Overall height	66 mm
Temperature	- 20 / + 60 °C
Standard	EN 12528
Weight	0.143 kg
Hardness of tread	Shore D 65
Load capacity (dynamic)	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○