

# AGILA

## 1470PAO100P30-11

EAN 4031582331509

Obrtni točkić, Kuciste od presovanog celika, pocinkovano , dupli kuglicni lezajevi u glavcini, rupa za vijak. Telo tocka od polipropilena , Omotac: Poliuretan , obican lezaj

# TENTE

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Precnik tocka.	100 mm
Sirina gazista.	25 mm
Sirina tocka	44 mm
Centralna rupa.	11 mm
Kupola -Ø	41 mm
Dislokacija	28 mm
Otpor okretanju.	156 mm
Sveukupna visina.	125 mm
Temperatura	- 20 / + 60 °C
Standard	EN 12530
Tezina	0.259 kg
Radijus okretanja	78 mm
Tvrdoća omotaca	Shore D 40
Dinamička nosivost.	70 kg
Statička nosivost.	140 kg

### Advantages at a glance

Otpor okretanju	● ● ● ○ ○
Buka pri okretanju	● ● ● ○ ○
trenje , habanje	● ● ● ● ○
zastita od korozije	● ● ● ○ ○