

# AGILA

## 1470PAO100P50

EAN 4031582331523

Obrtni točkić, Kuciste od presovanog celika, pocinkovano , dupli kuglicni lezajevi u glavcini, Priključak ploca.. Telo tocka od polipropilena , Omotac: Poliuretan , obican lezaj

# TENTE

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Precnik tocka.	100 mm
Sirina gazista.	25 mm
Sirina tocka	44 mm
Dimenzije ploce.	77 x 67 mm
Raspored rupa na ploci.	61,5/56 x 51,5/46,5 mm
Rupa na ploci.	8,5 mm
Kupola -Ø	41 mm
Dislokacija	28 mm
Otpor okretanju.	156 mm
Sveukupna visina.	125 mm
Temperatura	- 20 / + 60 °C
Standard	EN 12530
Tezina	0.309 kg
Radius okretanja	78 mm
Tvrdoca omotaca	Shore D 40
Dinamicka nosivost.	70 kg
Staticka nosivost.	140 kg

### Advantages at a glance

Otpor okretanju	● ● ● ○ ○
Buka pri okretanju	● ● ● ○ ○
trenje , habanje	● ● ● ● ○
zastita od korozije	● ● ● ○ ○

### Structure & Mounting

