

AGILA

1477PAO100P30-11

EAN 4031582331516

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel centre made of Polypropylene, Tread: Polyurethane, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	100 mm
Wheel width	25 mm
Castor width	44 mm
Centre hole	11 mm
Dome-Ø	41 mm
Offset	28 mm
Swivel Interference	174 mm
Overall height	125 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.328 kg
Swivel Radius	87 mm
Hardness of tread	Shore D 40
Load capacity	70 kg
Load capacity (static)	140 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○