

# AGILA

2477PJO075P30-11

EAN 4031582050363

Okretni tocak sa potpunom kocnicom , zadnji deo tocka, Kuciste od presovanog celika, pocinkovano , dupli kuglicni lezajevi u glavcini, rupa za vijak. Telo tocka od polipropilena , Omotac: TENTEprene (termoplasticna guma), siva - ne ostavlja trag , obican lezaj Tockovi mogu biti montirani sa standardnim srafovimima , sa razlicitim duzinama srafova.

**TENTE**

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Tehnicki podaci

Precnik tocka.	75 mm
Sirina gazista.	25 mm
Sirina tocka	43 mm
Centralna rupa.	11 mm
Kupola - $\emptyset$	43 mm
Dislokacija	24 mm
Otpor okretanju.	160 mm
Sveukupna visina.	100 mm
Temperatura	- 20 / + 60 °C
Standard	EN 12530
Tezina	0.267 kg
Radijus okretanja	80 mm
Tvrdoća omotaca	Shore A 87
Dinamička nosivost.	75 kg
Statička nosivost.	150 kg

## Advantages at a glance

Otpor okretanju	● ● ● ○ ○
Buka pri okretanju	● ● ● ○ ○
trenje , habanje	● ● ● ○ ○
zastita od korozije	● ● ● ○ ○

## Dimensions



## Structure & Mounting

