

AGILA

2478UAP100P50

EAN 4031582302417

Fiksirani točkić, Viljuska napravljena od presovanog celika, pocinkovana, Osovina tocka sa caurom, Priključak ploca..

Duza dimenzija ploce 90 van trake.

Telo tocka od poliamida , Omotac: POLiuretan , precizni kuglicni lezaj, sa ratkapnama

TENTE

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Tehnicki podaci

| | |
|-------------------------|------------------------|
| Precnik tocka. | 100 mm |
| Sirina gazista. | 32 mm |
| Sirina tocka | 60 mm |
| Dimenzije ploce. | 77 x 67 mm |
| Raspored rupa na ploci. | 61,5/56 x 51,5/46,5 mm |
| Rupa na ploci. | 8,5 mm |
| Kupola -Ø | 60 mm |
| Sveukupna visina. | 135 mm |
| Temperatura | - 25 / - 25 °C |
| Standard | EN 12530 |
| Tezina | 0.565 kg |
| Tvrdoca omotaca | Shore D 42 |
| Dinamicka nosivost. | 100 kg |
| Staticka nosivost. | 200 kg |

Dimensions



Advantages at a glance

| | |
|---------------------|-----------|
| Otpor okretanju | ● ● ● ○ ○ |
| Buka pri okretanju | ● ● ● ○ ○ |
| trenje , habanje | ● ● ● ● ○ |
| zastita od korozije | ● ● ● ○ ○ |

AGILA

2478UAP100P50

EAN 4031582302417



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

