

STYLEA

5920UOI075L51-10 DOM20

EAN 4031582310962

Obrtni točkić, Kuciste napravljeno od poliamida, "slepa" rupa za nameštajske nastavke. Telo tocka od poliamida , obican lezaj



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Tehnicki podaci

Precnik tocka.	75 mm
Sirina gazista.	8 mm
Sirina tocka	54 mm
Centralna rupa.	10 mm
Kupola -Ø	20 mm
Dislokacija	30 mm
Otpor okretanju.	124 mm
Sveukupna visina.	77 mm
Temperatura	- 20 / + 60 °C
Standard	EN 12528
Tezina	0.119 kg
Radijus okretanja	62 mm
Tvrdoca omotaca	Shore D 65
Dinamicka nosivost.	50 kg
Staticka nosivost.	100 kg

Advantages at a glance

Otpor okretanju	● ● ● ○ ○
Buka pri okretanju	● ● ● ○ ○
trenje , habanje	● ● ● ● ●
zastita od korozije	● ● ● ● ○

Structure & Mounting

