

# ALPHA

## 8470UOO200P63

EAN 4031582312737

Obrtni točkić, Kuciste napravljeno od nerđajućeg celika, dupli kuglični lezajevi u okretnoj glavi, osovina sa caurom, Priključak ploca.. Telo tocka od poliamida , obican lezaj

# TENTE

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Precnik tocka.	200 mm
Sirina gazista.	50 mm
Sirina tocka	96 mm
Dimenzije ploce.	137 x 105 mm
Raspored rupa na ploci.	105 x 80/75 mm
Rupa na ploci.	11 mm
Kupola -Ø	96 mm
Dislokacija	55 mm
Otpor okretanju.	310 mm
Sveukupna visina.	240 mm
Temperatura	- 40 / + 80 °C
Standard	EN 12532
Tezina	2.041 kg
Radius okretanja	155 mm
Tvrdoca omotaca	Shore D 75
Dinamicka nosivost.	500 kg
Staticka nosivost.	1000 kg

### Advantages at a glance

Otpor okretanju	● ● ● ○ ○
Buka pri okretanju	● ● ● ○ ○
trenje , habanje	● ● ● ● ●
zastita od korozije	● ● ● ● ●

### Dimensions



### Structure & Mounting



# ALPHA

8470UOO200P63

EAN 4031582312737



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

