

ICS

5321UAP100R05-18X62

EAN 4031582367652



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	ICS
Housing type	Swivel castor with directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.39 in
Overall weight	1.34 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	Integrated threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (D)	42 Shore D

HOUSING

Material	Polyamide
Fork shape	Slim
Swivel bearing	Stem, swiveling
Offset	1.46 in
Swivel interference	7.83 in

FITTING

Fitting type	Solid stem, round
Bolt diameter	0.71 in
Bolt length	2.44 in



IF
Design
Award

TECHNICAL DRAWINGS

