

## STORA

2370PJJ125P30-13

EAN 4031582300338



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance ● ● ● ○ ○

Movement noise ● ● ● ○ ○

Attrition ● ● ● ○ ○

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	155 mm
Overall weight	0.662 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	100.5 mm
Swivel interference	201 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# STORA

2370PJJ125P30-13

EAN 4031582300338



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

