

OMIKRON

9258STP300P66

EAN 4031582314137
Order number 00830234



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Omikron |
| Housing type | Fixed castor |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 6878.41 lb |
| Load capacity at 6 km/h | 5732.01 lb |
| Load capacity Static | 11464.02 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 14.57 in |
| Overall weight | 74.53 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Sheet steel, heavy |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 11.81 in |
| Tread width | 3.94 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|------------|----------------------------------|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Straight |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 9.84 in |
| Plate width | 7.87 in |
| Plate hole length (Maximum) | 8.27 in |
| Plate hole width (Maximum) | 6.3 in |
| Plate hole diameter | 0.67 in |

TECHNICAL DRAWINGS

