

ELASTECH

JFC125X32-Ø8

EAN 4031582319941
Order number 00024549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.5 lb

WHEEL

Body material	Zinc die-cast
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Axle hole diameter	0.31 in
Hub length	1.4 in
Hardness of tread (A)	75 Shore A

ELASTECH

JFC125X32-Ø8

EAN 4031582319941
Order number 00024549



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

