

ELASTECH

JFC150X32-Ø8

EAN 4031582319958

Broj porudžbine 00024889



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Elastech

Tip kućišta Tocak

Standard EN12530 - Kastori uređaja

Nosivost na 3 km/h 150 kg

Statički Nosivost 300 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 85 °C

Ukupna težina 0,926 kg

TOCAK

Materijal za telo	Cink die-cast
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglicni lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
dužina glavcine	35,5 mm
Teškoća gazećeg omotac (A)	75 Šor A

ELASTECH

JFC150X32-Ø8

EAN 4031582319958
Broj porudžbine 00024889



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

