

BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732
Order number 00002759



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Load capacity Static	250 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.064 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	34 mm
Axle hole diameter	12.1 mm
Hub length	44.4 mm
Hardness of tread (D)	65 Shore D

BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732
Order number 00002759



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

