

# BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732  
Order number 00002759



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	275.58 lb
Load capacity Static	551.16 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.14 lb

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.34 in
Axle hole diameter	0.48 in
Hub length	1.75 in
Hardness of tread (D)	65 Shore D

# BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732  
Order number 00002759



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

