

# BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817  
Order number 00030948



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	48 mm
Body width	40 mm
Hardness of tread (D)	65 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Basetech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.207 kg

# BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817  
Order number 00030948



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

