

BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817
Broj porudžbine 00030948

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,207 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajući lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	12 mm
dužina glavcine	48 mm
Širina tela	40 mm
Teškoća gazećeg omotac (D)	65 Šor D

BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817
Broj porudžbine 00030948



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

