

PRODUCT INFORMATION

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Order number 00002304



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	1.006 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	20.1 mm
Hub length	60 mm
Hardness of tread (D)	75 Shore D

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Order number 00002304



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

