

ALPHA

3470PVR200P30-13

EAN 4031582304244



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip kućišta	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	235 mm
Ukupna težina	2,598 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
Teškoća gazećeg omotac (A)	85 Šora A

KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	55 mm
okretni radijus	155 mm
Otpor okretanju	310 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

ALPHA

3470PVR200P30-13

EAN 4031582304244



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

