

# ALPHA

3470UER200P30-13

EAN 4031582304374



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	235 mm
Overall weight	2.362 kg

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	155 mm
Swivel interference	310 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA

3470UER200P30-13

EAN 4031582304374



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

