

ALPHA

3477UER160P30-13

EAN 4031582305838



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Housing type | Swivel castor with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 440.92 lb |
| Load capacity Static | 881.85 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 7.68 in |
| Overall weight | 5.15 lb |

WHEEL

| | |
|-----------------------|---------------------------------|
| Body material | Polyamide |
| Tread material | Elastic tire, black, vulcanized |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 6.3 in |
| Tread width | 1.81 in |
| Hardness of tread (A) | 64 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 2.36 in |
| Swivel radius | 6.57 in |
| Swivel interference | 13.15 in |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.51 in |

ALPHA

3477UER160P30-13

EAN 4031582305838



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

