

# ZETA

4688UOO160P63

EAN 4031582308334  
Order number 00805474



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity at 6 km/h	400 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall weight	1.521 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	117 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ZETA

4688UOO160P63

EAN 4031582308334  
Order number 00805474



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

