

KAPPA

9682TOO250P63

EAN 4031582316025
Order number 00830638



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2645.54 lb
Load capacity at 6 km/h	2204.62 lb
Load capacity Static	4409.24 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	12.01 in
Overall weight	11.66 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	2.4 in
Swivel interference	14.65 in

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

KAPPA

9682TOO250P63

EAN 4031582316025
Order number 00830638



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

