

# NOVATECH

FTP200X80-Ø25 HL90

EAN 4031582329681



Image may differ from the original product

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	3.15 in
Axle hole diameter	0.98 in
Hub length	3.54 in
Hardness of tread (A)	92 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3703.76 lb
Load capacity at 6 km/h	3086.47 lb
Load capacity Static	6172.94 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	15.56 lb

# NOVATECH

FTP200X80-Ø25 HL90

EAN 4031582329681

## TECHNICAL DRAWINGS

---

