

NOVATECH

FTP200X80-Ø25 HL90

EAN 4031582329681



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	80 mm
dimenzija rupa osovina	25 mm
dužina glavcine	90 mm
Teškoća gazećeg omotac (A)	92 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip kućišta	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	1680 kg
Nosivost na 6 km/h	1400 kg
Statički Nosivost	2800 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	7,056 kg

TEHNIČKI CRTEŽI

