

## B10-11x20 / 8

EAN 4031582317596

metalno vreteno sa osiguracem



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Metalno vreteno sa prstenom.	11 x 20 mm
Sveukupna visina.	4.5 mm
Tezina	0.029 kg
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○