

P10-40x16 / 8

EAN 4031582320107

stem with U-shaped plate



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Size of Plate	40 x 16 mm
Plate hole centres	32 mm
Plate hole	4 mm
Overall height	8 mm
Weight	0.024 kg
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○