

## P10-40x25 / 8

EAN 4031582320145

metalno vreteno za plocom U oblika



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

|                         |            |
|-------------------------|------------|
| Dimenzije ploce.        | 40 x 25 mm |
| Raspored rupa na ploci. | 32 mm      |
| Rupa na ploci.          | 4 mm       |
| Sveukupna visina.       | 8 mm       |
| Tezina                  | 0.03 kg    |
| Dinamicka nosivost.     | 40 kg      |
| Staticka nosivost.      | 80 kg      |

### Advantages at a glance

|                     |           |
|---------------------|-----------|
| Otpor okretanju     | ○ ○ ○ ○ ○ |
| Buka pri okretanju  | ○ ○ ○ ○ ○ |
| trenje , habanje    | ○ ○ ○ ○ ○ |
| zastita od korozije | ● ● ● ○ ○ |