

P11-40x25 / 8

EAN 4031582320206

Metalno vreteno sa plocom L oblika



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Tehnicki podaci

Dimenzije ploce.	40 x 25 mm
Raspored rupa na ploci.	32 mm
Rupa na ploci.	4 mm
Sveukupna visina.	8 mm
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○