

R10-8x20 / 8

EAN 4031582321470

cev sa navojem



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Tehnicki podaci

Metalno vreteno sa prstenom.	8 x 20 mm
Sveukupna visina.	3.5 mm
Tezina	0.02 kg
Ogrlica -Ø	13 mm
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○