



BETTER MOBILITY. BETTER LIFE.

## R20-10x29 / 7 without rips

EAN 4031582321524

plastican okrugli cep



Picture may differ from original product

### Tehnicki podaci

Bolcna - $\emptyset$	10 mm
Duzina bolcne.	29 mm
Sveukupna visina.	3.5 mm
Tezina	0.001 kg
Ogrlica - $\emptyset$	18 mm
Dinamicka nosivost.	30 kg
Staticka nosivost.	60 kg

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○