

## R20-12x27 / 7

EAN 4031582321555

plastican okrugli cep



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Bolcna - $\emptyset$	12 mm
Duzina bolcne.	27 mm
Sveukupna visina.	5.5 mm
Tezina	0.002 kg
Ogrlica - $\emptyset$	17 mm
Dinamicka nosivost.	30 kg
Staticka nosivost.	60 kg

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○