

## R40-17x17 / 11

EAN 4031582090161

plasticne caure (kvadratne)



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

### Tehnicki podaci

Bolcna -Ø	17 mm
Sveukupna visina.	36 mm
Tezina	0.005 kg
Ogrlica -Ø	19 mm
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

### Dimensions



Bezeichnung	A	B	C
R40-16x16	16	20	36
R40-17x17	17	19	36
R40-18x18	18	20	36
R40-21x21	21	23,5	36
R40-22x22	22	24,5	36
R40-23x23	23	25,5	36
R40-26x26	26	30	36

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○