



BETTER MOBILITY. BETTER LIFE.

S10-7x25 / 8

EAN 4031582321852

threaded stem, for profile acc. to DIN 1998



Picture may differ from original product

Technical Data

| | |
|-------------------------|------------|
| Threaded stem | 25 x 51 mm |
| Overall height | 8 mm |
| Weight | 0.023 kg |
| Load capacity (dynamic) | 40 kg |
| Load capacity (static) | 80 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ○ ○ ○ ○ ○ |
| Movement noise | ○ ○ ○ ○ ○ |
| Attrition | ○ ○ ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |