S70-10x15 / 10

EAN 4031582321876

threaded stem with hexagon neck





Picture may differ from original product

Technical Data

Threaded stem	M 10 x 15 mm
Overall height	6 mm
Weight	0.025 kg
Load capacity	80 kg
Load capacity (static)	160 kg

Advantages at a glance

Roll performance	00000
Movement noise	00000
Attrition	00000
Corrosion resistance	• • • 0 0