

S70-10x15 / 8

EAN 4031582321890

narezan vijak sa hexagonalnim vratom



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Tehnicki podaci

Navijeno vreteno.	M 10 x 15 mm
Sveukupna visina.	6 mm
Tezina	0.022 kg
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○