

## S70-6x25 / 8

EAN 4031582322002

narezan vijak sa hexagonalnim vratom



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Navijeno vreteno.	M 6 x 25 mm
Sveukupna visina.	6 mm
Tezina	0.02 kg
Dinamicka nosivost.	40 kg
Staticka nosivost.	80 kg

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○