



BETTER MOBILITY. BETTER LIFE.

S70-8x10 / 8

EAN 4031582322019

threaded stem with hex neck



Picture may differ from original product

Technical Data

Threaded stem	M 8 x 10 mm
Overall height	6 mm
Weight	0.018 kg
Load capacity (dynamic)	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○