

## S70-8x15 / 10

EAN 4031582322033

narezan vijak sa hexagonalnim vratom



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Tehnicki podaci

Navijeno vreteno.	M 8 x15 mm
Sveukupna visina.	6 mm
Tezina	0.025 kg
Dinamicka nosivost.	50 kg
Staticka nosivost.	100 kg

### Advantages at a glance

Otpor okretanju	○ ○ ○ ○ ○
Buka pri okretanju	○ ○ ○ ○ ○
trenje , habanje	○ ○ ○ ○ ○
zastita od korozije	● ● ● ○ ○