

PRODUCT INFORMATION

ELASTECH

UFP125X40-Ø8 BLUE

EAN 4031582323351
Order number 00000519



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	551.16 lb
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	1.1 lb

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Hardness of tread (A)	63 Shore A

ELASTECH

UFP125X40-Ø8 BLUE

EAN 4031582323351
Order number 00000519



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

