

DURATECH

UOO200X46-Ø20

EAN 4031582070132
Order number 00001775



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Axle hole diameter	20.1 mm
Hub length	58 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.595 kg

DURATECH

UOO200X46-Ø20

EAN 4031582070132
Order number 00001775



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

