

DURATECH

UOO200X46-Ø20

EAN 4031582070132
Order number 00001775



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 7.87 in |
| Tread width | 1.81 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.28 in |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Duratech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 1322.77 lb |
| Load capacity Static | 2645.54 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 1.31 lb |

DURATECH

UOO200X46-Ø20

EAN 4031582070132
Order number 00001775



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

