

# DURATECH

UOO160X40-Ø20

EAN 4031582070125  
Order number 00001874



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 160 mm                    |
| Tread width           | 40 mm                     |
| Axle hole diameter    | 20.1 mm                   |
| Hub length            | 58 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Duratech                      |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 500 kg                        |
| Load capacity Static        | 1000 kg                       |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.448 kg                      |

# DURATECH

UOO160X40-Ø20

EAN 4031582070125  
Order number 00001874



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

