

DURATECH

UOO100X36-Ø12

EAN 4031582070101
Broj porudžbine 00001720

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	36 mm
dimenzija rupa osovina	12,1 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,135 kg

DURATECH

UOO100X36-Ø12

EAN 4031582070101
Broj porudžbine 00001720



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

