

# DURATECH

UOO125X40-Ø12 HL 48

EAN 4031582323467

Broj porudžbine 00001793



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	12 mm
dužina glavcine	48,4 mm
Teškoća gazećeg omotac (D)	75 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,244 kg

# DURATECH

UOO125X40-Ø12 HL 48

EAN 4031582323467  
Broj porudžbine 00001793



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

