

SUPRATECH

PJO100X32-Ø12 HL44,4

EAN 4031582320411
Order number 00001800



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.129 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Axle hole diameter	12.3 mm
Hub length	44.4 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJO100X32-Ø12 HL44,4

EAN 4031582320411
Order number 00001800



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

