

DURATECH

UOR160X40-Ø20

EAN 4031582323566
Order number 00026850



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	1.27 lb

DURATECH

UOR160X40-Ø20

EAN 4031582323566
Order number 00026850



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

