

PURETECH

PVO080X35-Ø12

EAN 4031582321180
Broj porudžbine 00002663

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ○ ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	70 kg
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,151 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	35 mm
dimenzija rupa osovina	12,1 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVO080X35-Ø12

EAN 4031582321180
Broj porudžbine 00002663



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

